

M-800/60-20B



Max. load capacity at wrist: 60 kg



Max. reach: 2040 mm

FANUC

Robot		Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m ²)			Average Power consumption (kW)	Protection	
Series	Version						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia		Body standard/optional	Wrist & J3 arm standard/optional
M-800	B	60	2040	6	±0.015*	820	370	225	340	720	250	720	150	150	150	260	260	400	210/30	210/30	130/20	-	IP54	IP54

● standard ○ on request - not available () with hardware and/or software option * Meets ISO9283 standards

M-800/60-20B

High accuracy model



M-800/60-20B

