

M-950iA/500



Max. load capacity at wrist: 500 kg



Max. reach: 2830 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range [°] ***						Maximum speed [°/s]						Moments (N-m)/Inertia (kg-m ²)			Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia		Body standard/optional	Wrist & J3 arm standard/optional
M-950	iA	500	500	2830	6	± 0.08*	2500**	370	150	392	720	244	720	100	80	80	110	110	170	3420/ 1100	3420/ 1100	1850/ 445	5	IP54	IP67

● standard ○ on request - not available [] with hardware and/or software option * Based on ISO928 ** Without controller. *** During short distance motions, the axis speed may not reach the maximum value stated.

M-950iA/500

Standard model



M-950iA/500

