

M-2000iA/1700L



Max. load capacity
at wrist: 1700 kg




Max. reach:
4683 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m ²)			Protection		
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Body standard/optional	Wrist & J3 arm standard/optional
M-2000	iA	1700L	1700	4683	6	±0.27**	12500	330	160	165	720	240	720	20	14	14	18	18	40	29400/7500	29400/7500	8820/5500	8	IP54/ IP56	IP67

● standard ○ on request - not available () with hardware and/or software option ** Based on ISO9283

M-2000iA/1700L Long arm



M-2000iA/1700L

Rear side
Interference area

