

# M-410iC/315



Max. load capacity at wrist: 315 kg



Max. reach: 3143 mm

# FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m <sup>2</sup> )			Protection		
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia	Average Power consumption (kW)	Body standard/optional	Wrist & J3 arm standard/optional
M-410	iC	315	315	3143	4	±0.05**	1600 (1330)	360	144	136	720	-	-	90	100	110	195	-	-	155	-	-	3	IP54	IP54

(no pedestal) ● standard ○ on request - not available \*\* Based on ISO9283

M-410iC/315

Hollow wrist

Rear side  
Interference area



M-410iC/315

