

M-710iC/50



Max. load capacity at wrist: 50 kg



Max. reach: 2050 mm


FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m ²)			Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia		Body standard/optional	Wrist & J3 arm standard/optional
M-710	iC	50	50	2050	6	±0.03**	560	360	225	440	720	250	720	175	175	175	250	250	355	206/21	206/21	127/13	2.5	IP54/ IP67	IP67

● standard ○ on request - not available v ** Based on ISO9283

M-710iC/50

6-axis



M-710iC/50

