

M-710iC/70



Max. load capacity at wrist: 70 kg



Max. reach: 2050 mm


FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m ²)			Protection		
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Body standard/optional	Wrist & J3 arm standard/optional
M-710	iC	70	70	2050	6	±0.04**	560	360	225	440	720	250	720	160	120	120	225	225	225	294/30	294/30	147/15	2.5	IP54/ IP67	IP67

● standard ○ on request - not available v ** Based on ISO9283

M-710iC/70

6-axis



M-710iC/70

