

ARC Mate 120iD



Max. load capacity at wrist: 25 kg



Max. reach: 1831 mm

FANUC

Robot			Max. load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m ²)			Average Power consumption (kW)	Protection	
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia		Body standard/optional	Wrist & J3 arm standard/optional
ARC Mate	120iD	25	25	1831	6	±0.02**	250	340 (370)	260	458	400	360	900	210	210	265	420	420	720	52/2.4	52/2.4	32/1.2	1	IP54i	IP67

● standard ○ on request - not available ** Based on ISO9283

ARC Mate 120iD

Hollow wrist



ARC Mate 120iD

