

# M-950iA/500

**FANUC**



Max. load capacity  
at wrist: 500 kg



Max. reach:  
2830 mm

Series	Version	Type	Robot		Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°) ***						Maximum speed (°/s)						Moments (N·m)/Inertia (kg·m²)			Protection	
									J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/inertia	J5 Moment/inertia	J6 Moment/inertia	Average Power consumption (kW)	Body standard/optional
M-950	iA	500	500	2830	6	± 0.08*	2500**	370	150	392	720	244	720	100	80	80	110	110	170	3420/1100	3420/1100	1850/445	5	IP54	IP67

● standard    ○ on request    - not available    [ ] with hardware and/or software option    \* Based on ISO928    \*\* Without controller.    \*\*\* During short distance motions, the axis speed may not reach the maximum value stated.

M-950iA/500

Standard model



M-950iA/500

