

ARC Mate 100iD/8L



Max. load capacity at wrist: 8 kg



Max. reach: 2032 mm

FANUC

Robot			Max.load capacity at wrist (kg)	Reach (mm)	Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range (°)						Maximum speed (°/s)						Moments (N-m)/Inertia (kg-m ²)			Protection		
Series	Version	Type						J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/ Inertia	J5 Moment/ Inertia	J6 Moment/ Inertia	Average Power consumption (kW)	Body standard/optional	Wrist & J3 arm standard/optional
ARC Mate	100iD	8L	8	2032	6	±0.03**	180	340 (370)	235	455	380	360	900	210	210	265	400	420	720	16.1/.63	16.1/.63	5.9/.061	1	IP54/ IP55	IP67

● standard ○ on request - not available ** Based on ISO9283

ARC Mate 100iD/8L Long arm, Hollow wrist



ARC Mate 100iD/8L

