

M-710iD/70

FANUC



Max. load capacity
at wrist: 70 kg



Max. reach:
2104 mm

Series	Version	Type	Max.load capacity at wrist [kg]	Reach [mm]	Controlled axes	Repeatability [mm]	Mechanical weight [kg]	Motion range [°] ***						Maximum speed [°/s]						Moments [N·m]/Inertia [kg·m ²]		Protection			
								J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6	J4 Moment/Inertia	J5 Moment/Inertia	J6 Moment/Inertia	Average Power consumption [kW]	Body standard/optional	Wrist & J3 arm standard/optional
M-710	iD	70	70	2104	6	± 0.03*	580**	370	225	440	720	250	720	180	180	180	260	260	370	300/30	300/30	150/15	2.5	IP54/IP67	IP67

● standard ○ on request - not available * Based on ISO9283 **Without controller ***During short distance motions, the axis speed may not reach the maximum value stated

M-710iD/70



M-710iD/70

